



HLM-250

Hand Lens Meter



New Technologies And Powerful Functions
Simple operation interface provides
with accurate operation experience.

SHANGHAI LINK INSTRUMENTS

Product Features :

- Internal reading focimeter
- Green LED illumination, Comfortable without glare,excellent durability.
- Solid mechanism of Lens pressing unit is applicable for measurement of lens from $\Phi 16\text{mm}$ to $\Phi 80\text{mm}$.
- Prism compensation device is optional, Support measurement of wide range of prism power from 5Δ to 20Δ .
- With wide tilting angle, HLM-250 is easy and simple to operate for both standing and sitting operators.with easy operation.



Product parameters:

🕒 Sphere	$-25.00\text{m}^{-1} \sim +25.00\text{m}^{-1}$
🕒 Step	$-5\text{m}^{-1} \sim +5\text{m}^{-1} : 0.125\text{m}^{-1}$;Other 0.25m^{-1}
🕒 Axis	$0^\circ \sim 180^\circ$, Step: 1°
🕒 Prism Basal Angle	$0^\circ \sim 180^\circ$, Step: 1°
🕒 Prism	Standard model: $0 \sim 5\text{cm/m}$, Step: 0.5cm/m Strengthened model: $5 \sim 20\text{cm/m}$, Step: 1cm/m
🕒 Lens diameter	$16\text{mm} \sim 80\text{mm}$
🕒 Regulation of ocular visibility	$-5.00\text{m}^{-1} \sim +5.00\text{m}^{-1}$
🕒 Dimensions	$280\text{mm(W)} \times 150\text{mm(D)} \times 450\text{mm(H)}$ / 4.9kg
🕒 Power Supply	Input DC $100\text{V} \sim 240\text{V}$, 50/60Hz, Output AC 6V 2A



Add.No.1101 Huyi Highway,Shanghai,201802,China
Tel.+86-21-69512871
Fax.+86-21-69512872
E-mail.sales@linkcsh.com
<https://linkeyegroup.com>

SHANGHAI LINK INSTRUMENTS CO.,LTD.